VISIONA

connected ultra-low hotel-style medical bed,

REF. COV58439BTD

The **VISIONA** ultra-low electric medical bed is a "connected" bed featuring 5 types of alarm

> 1 main alarm (included in the package): bed height - indicates incorrect bed height adjustment to limit the risk of resident falls and injuries

> 4 optional alarms: resident presence, bed rail position, brakes off and incontinence detection.

Intuitive operation thanks to the centralised controls on the Nurse Control unit fixed onto the bed.

The sensors necessary to resident safety are invisible, so there is no disruption in the room environment.

Technical specifications

ALERT - BED HEIGHT

A MEDIUNIC COMPANY

(INCLUDED AS STANDARD)

Detects if the bed is not in the safe low position (23 cm from the floor) Green light: bed in safe low position Red light: bed in an unsafe position

The visual alarm can be accompanied by an audible alarm

HEIGHT ADJUSTMENT LIFTING COLUMN < SPECIFIC TO FLOORE, VISIONA >

• The design with electric actuators integrated into the columns allows totally free access underneath the bed, improving the work of the staff and enabling productivity



• Customisable: wide selection of laminates and varnished solid woods

ACCESSORY ANCHORS

• 4 for drip holder • 2 for hand control pendant

(at the head of the bed) 4 for trapeze bar holder (at the head & foot of the bed)

WALL **BUMPERS**

· Aluminium wall bumpers (supplied) are easily screwed into the headboard

FUNCTIONS

MULTIFUNCTIONAL

 Variable height / Backrest (with autoregression) / Footrest (knee break) / TR/ATR / Cardiac chair position

RED BASE

 5 removable slats made of recycled ABS (optional) Compact laminate flat bed base

optional) SIDE RAILS

 3 concepts: half-length rails, 3/4length rails, or full-length rails.

(included), with the option to disable certain functions

• Nurse Control unit for caregivers (included)

• Intuitive wired hand control pendant

The edge flashes red if an alarm goes off

CONTROLS

EXTENSION

 Integrated in the foot of the bed with mattress extension rest (easy access and tool-free setup)

BRAKES

 Semi-centralised. bilateral at the head/foot

Multidirectional (360°) with double rollers, Ø 50 mm Base-covered for a "de-medicalized"

Key data

Variable height

SWL (patient weight) Empty weight (without accessories)

> Backrest angle Knee break TR/ANTI-TR angle

> > Extension

Dimensions (without side rails) Lying surface

Materials

Dual wheel castors

Supply voltage

Certification Standards 23 cm - 68 cm

220 kg (185 kg) 100 kg

• The emergency bed flat function

accessible bilateral handles

can be quickly activated using 2 easily

70° (max.) 30° (max.)

17° / 17° (max.)

12 cm

220 x 106 cm 200 x 90 cm

Steel, Solid wood, Laminate

360° / Ø 50 mm

100-230 V, 50/60 Hz

Max. 3.15 A

CE (REG (EU) 2017/745) NF EN 60601-2-52 NF EN 60601-1-2 NF EN 60601-1

Customisation and Accessories



the bed







Options



Chalk White

•115 mm Wall Protection Bumper – LSUGHBM •190 mm Wall Protection Bumper – LSUGHBFF •Under-Bed Night Light – LSUGHVEIL

•Headboard Reading Lamp - LSUGHLUMF



Polar Aland Pine



Space under the bed totally clear

< SPECIFIC TO FLOORE, VISIONA >

completely unobstructed access underneath

• The height adjustment system allows

Side rails available

Colour (bed frame)



- 3/4-length rails
- · Full-length rails

Hygiene & Disinfection

· Cleaning products must be sprayed on or applied with a disposable cloth · It is also recommended to start cleaning at the top and work down

Available Accessories

·Battery - LSUGHBATF

Retractable Trapeze Bar

•IV Pole with 4 Hooks •Flexible Remote Control Holder

•Urine Bag Holder (on 3/4 Side Rail)


•Grab Handle

Compressor Holder

Standard and Large-Loop Strap Fasteners

•3/4 Side Rail Extension





•Wooden Décor for 3/4 Side Rail

Transport Trolley



